

# JumpStart® Softback™



CASCADE  
daFO®

*AFO trimline, PF resist, DF free*

The JumpStart Softback is a prefabricated AFO providing comfortable control of moderate toe walking and knee hyperextension. The Softback's posterior pad and strap combination work together to resist excess plantarflexion beyond 2 degrees, while encouraging increased dorsiflexion.



## Key Features

**Soft yet durable padding sewn to flexible Dacron strap**  
strongly resists excess PF and encourages free DF.

**Dacron strap attaches to outer frame**  
for durability.

**Full-wrap inner liner**  
provides alignment control of the heel, midfoot, and forefoot.

**Inner liner tucks behind the padding**  
for added comfort.

**Solid outer foundation**  
provides additional support and heel stabilization. Available in polyethylene for moderate flexibility or co-poly for firm support.

**Prefabricated**  
sized by measurement using the Fast Fit sizing jig.


**Sizes:** 4.00 – 7.75 inches (0.25 inch increments)

## Designed for patients who:

- Exhibit a fully correctable foot position and fit within the product size range.
- Demonstrate mild to moderate excess plantarflexion presented as toe walking or knee hyperextension.
- Require some resistance to plantarflexion.
- Will benefit from full access to dorsiflexion.
- Present with moderate to strong pronation or supination and associated gait instability.
- May benefit from the sensory feedback provided by a fully contoured foot bed.



*Flexible Dacron strap*



*Inner liner tucks  
behind the padding*



**No casting needed!**

JS Softback Product Sheet Rev.02 (June 2025)

Helping kids lead healthier, happier lives®

Cascade Dafo, Inc.

1360 Sunset Avenue  
Ferndale, WA 98248

ph: 800.848.7332  
fax: 855.543.0092

intl: +1 360 543 9306  
[www.cascadedrafo.com](http://www.cascadedrafo.com)